



## Door Opening Dimensions



142mm (W) x 120 mm (H)

This dimension is the smallest area of the cat flap that a pet will have to pass through.


## Required Hole Dimensions



165 mm (W) x 171 mm (H)

The inner edge of the exterior frame can be used as a template to cut the hole required to fit the cat flap.


## Exterior Frame Dimensions



210 mm (W) x 210 mm (H)

This is the entire area taken up by the cat flap.

## Glass Mounting Dimensions




212 mm to 260 mm

When mounting into glass you will need to cut a hole between 212mm and 260mm in diameter.

Using the Glass mounting adaptor you will be able to securely insert the door into the hole and fix in place.

The total diameter of the cat flap mounting adaptor is 285mm.



## Tunnel Extension

If installing the product into a wall you may need to extend the pet doors tunnel. This can be easily done using multiple Tunnel Extenders.

The tunnel of the SureFlap Microchip Cat Flap/ DualScan Cat Flap is **70mm** long and **each tunnel extender adds 50mm** to the length of the pet door's tunnel.

